

Preview

We develop, manufacture and distribute emission spectrometers for precise and quick element analysis of metals and alloys. Equipped with state-of-the-art detector technology, the metal analyzer enables precise determination of the material composition at an attractive device price.

OLB ist ein deutsches, mittelständiges Unternehmen mit Sitz in Witten, Nordrhein-Westfalen. Vor über 40 Jahren wurde dort die

Our spectrometer software, OLBwin, whose parameters can be set to suit the tasks of the individual customer, contains materials

The OLB MVS 1000 spark emission spectrometer allows a versatile, flexible and fast analysis of all

OLB spectrometers use thermal compensation of a diffraction grating and an optical system frame placed in a vacuum chamber. In

The OLB VeOS is a high-performance, floor-standing full-spectrum direct-reading optical emission

What makes OLB spectrometers unique? OLB spectrometers are recognized for their excellent long-term stability,

The OLB GS1000-II is a high-performance, floor-standing spark optical emission spectrometer (OES)

Bei dem GS 1000-II, dem kleinsten Mitglied der OLB-Familie, handelt es sich um ein Ein-Matrix-Funkenemissions-Spektrometer für

Inbetriebnahme Anwenderunterstützung beginnt bei uns bereits während der Inbetriebnahme der Spektrometer bei unseren Kunden.

Our QSG 750-II spark emission spectrometer can also be called OLB's flagship model. This single- or

Beschreibung Bei dem GS 1000-II, dem kleinsten Mitglied der OLB-Familie, handelt es sich um ein Ein-Matrix-Funkenemissions

Ist das Spektrometer Teil eines automatisch arbeitenden Laboratoriums, z. B. zusammen mit einer Probenvorbereitungsmaschine

The OBLF OS.5c spark emission spectrometer enables precise determination of the material composition

OBLF Spectrometry develops, manufactures and distributes emission spectrometers for precise and quick element analysis of

Beschreibung Bei dem Funkenemissions-Spektrometer QSG 750-II kann man durchaus auch vom OBLF-Flaggschiff sprechen. Das

Featuring cutting-edge detector technology on the basis of semiconductor detectors that were specially developed for emission

Web: <https://www.supremeacademicresearch.co.za>

